



ADVANCED MIXING TECHNOLOGY

Created from the highest quality parts, the Unguator® uses sturdy variable mixing motors that keep speed fluctuations to a minimum and ensures consistent preparations every time.

The Unguator® technology offers a very quick and reliable system for creating batch sizes from 15 mL up to 1000mL. This mixing technology offers a closed system that optimizes the results of your formulation mixes plus minimizes cross-contamination and waste.

The Unguator® mixing blades were designed to “sweep” the inner chamber wall of the jar to maximize particle reduction. They offer a sharp leading edge to act as a grinding mechanism and to ensure product homogeneity.

The Unguator® product line also offers a patented push up bottom jar which serves unique functions throughout the mixing process.



The Unguator® Jars can be used for the following:

- Measuring unit
- Mixing chamber
- Storage container
- Unique dispensing jar

EXACTDOSE™



NEW, IMPROVED & EASY-TO-USE

The 0.5ml ExactDose™ dispensers are perfect for your metered dosing needs! Simply attach the ExactDose™ dispenser to the top of your Unguator™ Jar. Push the plunger up to fill the ExactDose™, twist the ExactDose™ key and then push the plunger again to dispense.

Call 405.329.6810 to receive a free sample today, or call your local distributor to place an order!