

WAY 5

Lock-To-Pole IV Lock Boxes by Health Care Logistics

Safety-conscious design details on HCL's exclusive Lock-to-Pole IV Lock Box protect infusions from tampering, prevent theft and improve patient safety.

| | | |
|------------------------------------|---|---|
| Chairman: | Gary Sharpe |  |
| CEO: | Connie Lewis | |
| VP of Business Development: | Cindy Bell | |
| Employees: | 200 | |
| Stock Symbol: | Private Company | |
| Toll Free Phone: | (800) 848-1633 | |
| Address: | PO Box 25 Circleville, OH 43113-0025 | |
| Website: | GoHCL.com | |

Company Background

Since 1978, Health Care Logistics has been a health care industry leader who specializes in manufacturing, packaging and distributing unique and hard-to-find products. In addition to the 10,000+ products available in HCL's inventory, the company provides free search and development services for non-inventory items. HCL offers small product quantities and has no minimum order requirements. Visit HCL online at GoHCL.com or call 1-800-848-1633 to speak live with HCL's friendly, knowledgeable customer service staff from 8 a.m. to 8 p.m. Eastern Time Monday through Friday.

Product Overview

HCL's Lock-To-Pole IV Lock Box is a durable, clear IV lock box that protects infusions, prevents theft and improves patient safety. This unique box with two locking options can only be removed from the pole when accessed from inside. Clamps with non-slip grips inside the box snap onto the pole and keep it in place. Once the door is closed and locked, the IV bag is secure. The Lock-To-Pole IV Lock Box requires a key or a keyless entry type lock. It locks to poles up to 7/8" diameter and accommodates bag sizes up to 1,000mL. Ports will be outside the box on 1,000mL IV bags. Dimensions: 7-1/2" W x 10-1/2" H x 4-1/2" D.

Ease of Use

Securely attaches to IV pole quickly and easily. Can only be removed from inside. Opens with standard key lock or four-digit code. See video demonstration at <http://GoHCL.com/ivb> for step-by-step instructions.

Features and Options

Clear, high-quality PETG plastic provides outstanding durability and allows at-a-glance monitoring of contents. Box interior features two locking clamps with non-slip grips that snap to the pole and keep it in place. Two locking options are available - key lock or keyless entry digital lock.

